



DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 8.8 M30X150

Article number	01200.300.150
Brand	-
UBB	950351163346
UNSPSC	31161620
EAN	8715492028105
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M30
Length	150 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-112
ISO	4014
ASME	B18.2.3.1M
DIN	931
NEN	1555

Technical Specification

b (min.): 125mm $L \leq 200$ mm	72
b (min.): $L > 200$ mm	85
b (min.): $L \leq 125$ mm	66
d-D	M30
k	18.7
L (mm)	150
P	3.5
s	46

Technical Drawing

