

## DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M5X30

|                |               |
|----------------|---------------|
| Article number | 01220.050.030 |
| Brand          | -             |
| UBB            | 952351328184  |
| UNSPSC         | 31161620      |
| EAN            | 8715492032966 |
| PKG. of 200    | Full Box Only |

### Technical Parameters

|                   |                                  |
|-------------------|----------------------------------|
| Diameter          | M5                               |
| Length            | 30 mm                            |
| Class             | 8.8                              |
| Driving features  | Hexagon                          |
| Head shape        | Hexagon head                     |
| Material          | Steel                            |
| Thread direction  | Right                            |
| Surface treatment | Zinc plated yellow<br>passivated |
| Thread            | Metric thread                    |

### Standards

|      |            |
|------|------------|
| NEN  | 1555       |
| ASME | B18.2.3.1M |
| DIN  | 931        |
| ISO  | 4014       |
| NF   | E25-112    |

### Technical Specification

|                           |     |
|---------------------------|-----|
| b (min.):<br>125mmL≤200mm | 22  |
| b (min.): L≤125mm         | 16  |
| d-D                       | M5  |
| k                         | 3.5 |
| L (mm)                    | 30  |
| P                         | 0.8 |
| s                         | 8   |

### Technical Drawing

