

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M8X150

Article number	01220.080.150
Brand	-
UBB	954351334345
UNSPSC	31161620
EAN	8715492033406
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	150 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	931
ISO	4014
ASME	B18.2.3.1M
NEN	1555
NF	E25-112

Technical Specification

b (min.): 125mm $L \leq 200$ mm	28
b (min.): $L \leq 125$ mm	22
d-D	M8
k	5.3
L (mm)	150
P	1.25
s	13

Technical Drawing

