

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M10X110/S=17

Article number	01220.100.110
Brand	-
UBB	952351328424
UNSPSC	31161620
EAN	8715492033604
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	110 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ISO	4014
NEN	1555
DIN	931
NF	E25-112
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	110
P	1.5
s	17

Technical Drawing

