

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M12X45/S=19

Article number	01220.120.045
Brand	-
UBB	950351169129
UNSPSC	31161620
EAN	8715492033734
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	45 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NEN	1555
NF	E25-112
ISO	4014
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	45
P	1.75
s	19

Technical Drawing

