

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M12X180/S=19

Article number	01220.120.180
Brand	-
UBB	952351982238
UNSPSC	31161620
EAN	8715492033901
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	180 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NF	E25-112
ISO	4014
NEN	1555
ASME	B18.2.3.1M
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	180
P	1.75
s	19

Technical Drawing

