

## Hexagon head bolt DIN 931 Steel Zinc plated yellow passivated 8.8 M14X55/S=22



Article number	01220.140.055
Brand	-
UBB	952351204336
UNSPSC	31161620
EAN	8715492033987
PKG. of 50	Full Box Only

### Technical Parameters

Diameter (d-D)	M14
Length (L) (mm)	55
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread
Wrench width (s) (mm)	22

### Standards

NF	E25-112
DIN	931
ASME	B18.2.3.1M
ISO	4014

### Technical Specification

b (min.): 125mm <math>L \leq 200\text{mm}</math>	40
b (min.): $L > 200\text{mm}$	53
b (min.): $L \leq 125\text{mm}$	34
k	8.8
P	2
s	22

### Technical Drawing

