

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M14X70/S=22

Article number	01220.140.070
Brand	-
UBB	950351170275
UNSPSC	31161620
EAN	8715492034014
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	70 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	931
ISO	4014
NEN	1555
NF	E25-112
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	70
P	2
s	22

Technical Drawing

