

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M16X75

Article number	01220.160.075
Brand	-
UBB	952351810397
UNSPSC	31161620
EAN	8715492034199
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	75 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NF	E25-112
ISO	4014
ASME	B18.2.3.1M
DIN	931
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	75
P	2
s	24

Technical Drawing

