

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M20X120

Article number	01220.200.120
Brand	-
UBB	950351172099
UNSPSC	31161620
EAN	8715492034601
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	120 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NF	E25-112
ISO	4014
DIN	931
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	120
P	2.5
s	30

Technical Drawing

