

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M20X180

Article number	01220.200.180
Brand	-
UBB	952351255239
UNSPSC	31161620
EAN	8715492034663
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M20
Length	180 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	931
ASME	B18.2.3.1M
NEN	1555
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	180
P	2.5
s	30

Technical Drawing

