

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 8.8 M24X90



Article number	01220.240.090
Brand	-
UBB	950351172412
UNSPSC	31161620
EAN	8715492034939
PKG. of 10	Full Box Only

Technical Parameters

Diameter (d-D)	M24
Length (L) (mm)	90
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NF	E25-112
ASME	B18.2.3.1M
ISO	4014
DIN	931

Technical Specification

b (min.): 125mm<L≤200mm	60
b (min.): L>200mm	73
b (min.): L≤125mm	54
k	15
P	3
s	36

Technical Drawing

