

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M24X110

Article number	01220.240.110
Brand	-
UBB	952351982808
UNSPSC	31161620
EAN	8715492034953
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	110 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NEN	1555
NF	E25-112
ASME	B18.2.3.1M
ISO	4014
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	110
P	3
s	36

Technical Drawing

