

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 8.8 M24X160



Article number	01220.240.160
Brand	-
UBB	950351172826
UNSPSC	31161620
EAN	8715492035004
PKG. of 10	Full Box Only

Technical Parameters

Diameter (d-D)	M24
Length (L) (mm)	160
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	931
ISO	4014
NF	E25-112
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm<L≤200mm	60
b (min.): L>200mm	73
b (min.): L≤125mm	54
k	15
P	3
s	36

Technical Drawing

