

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M24X180

Article number	01220.240.180
Brand	-
UBB	953351786793
UNSPSC	31161620
EAN	8715492035028
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	180 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	931
ASME	B18.2.3.1M
ISO	4014
NEN	1555
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	180
P	3
s	36

Technical Drawing

