

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M30X130

Article number	01220.300.130
Brand	-
UBB	952351904935
UNSPSC	31161620
EAN	8715492035264
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M30
Length	130 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ISO	4014
NEN	1555
ASME	B18.2.3.1M
DIN	931
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	72
b (min.): L200mm	85
b (min.): L≤125mm	66
d-D	M30
k	18.7
L (mm)	130
P	3.5
s	46

Technical Drawing

