

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M30X200

Article number	01220.300.200
Brand	-
UBB	953351869383
UNSPSC	31161620
EAN	8715492035325
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M30
Length	200 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	931
ASME	B18.2.3.1M
NF	E25-112
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	72
b (min.): L200mm	85
b (min.): L≤125mm	66
d-D	M30
k	18.7
L (mm)	200
P	3.5
s	46

Technical Drawing

