

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M33X160

Article number	01220.330.160
Brand	-
UBB	954351336654
UNSPSC	31161620
EAN	8715492035424
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M33
Length	160 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ISO	4014
ASME	B18.2.3.1M
NF	E25-112
DIN	931
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	78
b (min.): L200mm	91
b (min.): L≤125mm	72
d-D	M33
k	21
L (mm)	160
P	3.5
s	50

Technical Drawing

