

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M33X180

Article number	01220.330.180
Brand	-
UBB	954351336738
UNSPSC	31161620
EAN	8715492035448
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M33
Length	180 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NEN	1555
DIN	931
NF	E25-112
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	78
b (min.): L200mm	91
b (min.): L≤125mm	72
d-D	M33
k	21
L (mm)	180
P	3.5
s	50

Technical Drawing

