

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M33X200

Article number	01220.330.200
Brand	-
UBB	954351336811
UNSPSC	31161620
EAN	8715492035455
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M33
Length	200 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ASME	B18.2.3.1M
DIN	931
ISO	4014
NF	E25-112
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	78
b (min.): L200mm	91
b (min.): L≤125mm	72
d-D	M33
k	21
L (mm)	200
P	3.5
s	50

Technical Drawing

