

ISO 4014 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Cr(III), Class 8.8

Article number	01224.060.040
Brand	-
UBB	500648268810
UNSPSC	31161620
EAN	8717077232549
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	40 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

Standards

ISO	4014
ASME	B18.2.3.1M
DIN	931
NEN	1555
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
k	4
L (mm)	40
P	1
s	10

Technical Drawing

