

ISO 4014 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated Cr(III), Class 8.8

Article number	01224.240.100
Brand	-
UBB	500648278553
UNSPSC	31161620
EAN	8717077233515
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	100 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

Standards

ISO	4014
ASME	B18.2.3.1M
NEN	1555
DIN	931
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	100
P	3
s	36

Technical Drawing

