

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 8.8 M6X60



Article number 01226.060.060

Brand -

UBB 500571899904

UNSPSC 31161620

EAN 8715494282437

PKG. of 200 Full Box Only

Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	60
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr(VI) free - flZn/nc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ISO	4014
ASME	B18.2.3.1M
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mm<L≤200mm	24
b (min.): L≤125mm	18
k	4
P	1
s	10

Technical Drawing

