

DIN 933 Fully Threaded Metric Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M20X140

Article number	01230.200.140
Brand	-
UBB	953351864665
UNSPSC	31161620
EAN	8715492037794
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	140 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ISO	4017
NEN	1568
ASME	B18.2.3.1M
NF	E25-114
DIN	933

Technical Specification

d-D	M20
k	12.5
L (mm)	140
P	2.5
s	30

Technical Drawing

