

DIN 933 Fully Threaded Metric Hexagon Head Bolt, Zinc Flake Cr6+ Free, Class 8.8 M4X25

Article number	01236.040.025
Brand	-
UBB	500571916088
UNSPSC	31161620
EAN	8715494288606
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	25 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	933
ASME	B18.2.3.1M
NEN	1568
NF	E25-114
ISO	4017

Technical Specification

d-D	M4
k	2.8
L (mm)	25
P	0.7
s	7

Technical Drawing

