

DIN 933 Fully Threaded Metric Hexagon Head Bolt, Zinc Flake Cr6+ Free, Class 8.8 M5X25

Article number	01236.050.025
Brand	-
UBB	500571916658
UNSPSC	31161620
EAN	8715494288668
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	25 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

NF	E25-114
ASME	B18.2.3.1M
DIN	933
NEN	1568
ISO	4017

Technical Specification

d-D	M5
k	3.5
L (mm)	25
P	0.8
s	8

Technical Drawing

