

DIN 933 Fully Threaded Metric Hexagon Head Bolt, Zinc Flake Cr6+ Free, Class 8.8 M10X45

Article number	01236.100.045
Brand	-
UBB	500571920288
UNSPSC	31161620
EAN	8715494276597
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	45 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ASME	B18.2.3.1M
NF	E25-114
DIN	933
ISO	4017
NEN	1568

Technical Specification

d-D	M10
k	6.4
L (mm)	45
P	1.5
s	17

Technical Drawing

