



DIN 960 Partially Threaded Metric Fine Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M12X1,50X50/S=19

Article number	01240.120.050
Brand	-
UBB	951351602168
UNSPSC	31161620
EAN	8715492039132
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	50 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric fine thread

Standards

DIN	960
ISO	8765
NF	E25-152
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	50
P	1.5
s	19

Technical Drawing

