



DIN 960 Partially Threaded Metric Extra Fine Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M10X1,00X45/S=17

Article number	01241.100.045
Brand	-
UBB	951351603984
UNSPSC	31161620
EAN	8715492039484
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	45 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric extra fine thread

Standards

DIN	960
NF	E25-152
ISO	8765
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	45
P	1
s	17

Technical Drawing

