



DIN 960 Partially Threaded Metric Extra Fine Hexagon Head Bolt, Zinc Plated Yellow Passivated, Class 8.8 M20X1,50X110

Article number	01241.200.110
Brand	-
UBB	951351592591
UNSPSC	31161620
EAN	8715492039781
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	110 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric extra fine thread

Standards

NF	E25-152
DIN	960
ISO	8765
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	110
P	1.5
s	30

Technical Drawing

