

Hexagon nut DIN 934 Steel Zinc plated with thick Cr(III) passivation |8| M8

Article number	01325.080.001
Brand	-
UBB	500505355957
UNSPSC	31161727
EAN	8715494207928
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M8
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

Standards

NEN	1560
NF	E25-401
DIN	934

Technical Specification

d-D	M8
m	6.5
P	1.25
s	13

Technical Drawing

