

## DIN 931 Partially Threaded Metric Hexagon Head Bolt, Hot Dip Galvanised, Class 8.8 M10X50/S=17

Article number	01400.100.050
Brand	-
UBB	950351188509
UNSPSC	31161620
EAN	8715492408228
PKG. of 50	Full Box Only

### Technical Parameters

Diameter	M10
Length	50 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

### Standards

NEN	1555
NF	E25-112
ASME	B18.2.3.1M
DIN	931
ISO	4014

### Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45

### Technical Drawing

b (min.): $L \leq 125\text{mm}$	26
d-D	M10
k	6.4
L (mm)	50
P	1.5
s	17

