

## DIN 931 Partially Threaded Metric Hexagon Head Bolt, Hot Dip Galvanised, Class 8.8 M10X90/S=17

Article number	01400.100.090
Brand	-
UBB	950351189267
UNSPSC	31161620
EAN	8715492408297
PKG. of 50	Full Box Only

### Technical Parameters

Diameter	M10
Length	90 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info  
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

### Standards

DIN	931
ISO	4014
NEN	1555
NF	E25-112
ASME	B18.2.3.1M

### Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45

### Technical Drawing

b (min.): $L \leq 125\text{mm}$	26
d-D	M10
k	6.4
L (mm)	90
P	1.5
s	17

