


Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M12X60/S=19



Article number	01400.120.060
----------------	---------------

Brand	-
-------	---

UBB	950351190562
-----	--------------

UNSPSC	31161620
--------	----------

EAN	8715492408501
-----	---------------

PKG. of 25	Full Box Only
------------	---------------

Technical Parameters

Diameter (d-D)	M12
Length (L) (mm)	60
Class	8.8
Driving features	Hexagon
Extra info	ISO metric
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Wrench width (s) (mm)	19

Standards

ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014

Info ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.

b (min.): 125mm <math>< L \leq 200\text{mm}</math>	36
b (min.): $L > 200\text{mm}$	49
b (min.): $L \leq 125\text{mm}$	30
k	7.5
P	1.75
s	19

