

## DIN 931 Partially Threaded Metric Hexagon Head Bolt, Hot Dip Galvanised, Class 8.8 M30X220

Article number	01400.300.220
Brand	-
UBB	951351597475
UNSPSC	31161620
EAN	8715492409768
PKG. of 5	Full Box Only

### Technical Parameters

Diameter	M30
Length	220 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

### Standards

DIN	931
ISO	4014
NF	E25-112
NEN	1555
ASME	B18.2.3.1M

### Technical Specification

b (min.): 125mmL≤200mm	72
b (min.): L200mm	85

### Technical Drawing

b (min.): $L \leq 125\text{mm}$	66
d-D	M30
k	18.7
L (mm)	220
P	3.5
s	46

