

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M30X220



Article number 01400.300.220

Brand -

UBB 951351597475

UNSPSC 31161620

EAN 8715492409768

PKG. of 5 Full Box Only

Technical Parameters

Diameter (d-D)	M30
Length (L) (mm)	220
Class	8.8
Driving features	Hexagon
Extra info	ISO metric
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Info	ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.

Standards

ASME	B18.2.3.1M
NF	E25-112
ISO	4014
DIN	931

Technical Specification

b (min.): 72
125mm < L ≤ 200mm

Technical Drawing

b (min.): $L > 200\text{mm}$ 85

b (min.): $L \leq 125\text{mm}$ 66

k 18.7

P 3.50

s 46

