

DIN 933 Fully Threaded Metric Hexagon Head Bolt, Hot Dip Galvanised, Class 8.8 M20X30

Article number	01410.200.030
Brand	-
UBB	500621734192
UNSPSC	31161620
EAN	8715494504027
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	30 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

ISO	4017
NEN	1568
ASME	B18.2.3.1M
DIN	933
NF	E25-114

Technical Specification

d-D	M20
k	12.5
L (mm)	30

Technical Drawing

P	2.5
s	30

