

DIN 933 Fully Threaded Metric Hexagon Head Bolt, Hot Dip Galvanised, Class 8.8 M20X75

Article number	01410.200.075
Brand	-
UBB	500644663246
UNSPSC	31161620
EAN	8717077015210
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	75 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

NEN	1568
DIN	933
ASME	B18.2.3.1M
ISO	4017
NF	E25-114

Technical Specification

d-D	M20
k	12.5
L (mm)	75

Technical Drawing

P	2.5
s	30

