

## DIN 933 Fully Threaded Metric Hexagon Head Bolt, Hot Dip Galvanised, Class 8.8 M27X90

Article number	01410.270.090
Brand	-
UBB	954351243181
UNSPSC	31161620
EAN	8715492410849
PKG. of 10	Full Box Only

### Technical Parameters

Diameter	M27
Length	90 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info  
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

### Standards

DIN	933
NEN	1568
NF	E25-114
ASME	B18.2.3.1M
ISO	4017

### Technical Specification

d-D	M27
k	17
L (mm)	90

### Technical Drawing

P	3
s	41

