

## DIN 933 Fully Threaded Metric Hexagon Head Bolt, Oversized Hot Dip Galvanised, Class 8.8 M16X40

Article number	01430.160.040
Brand	-
UBB	950351210865
UNSPSC	31161620
EAN	8715492412461
PKG. of 50	Full Box Only

### Technical Parameters

Diameter	M16
Length	40 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

#### Info

Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized). oversized

### Standards

NF	E25-114
NEN	1568
DIN	933
ASME	B18.2.3.1M
ISO	4017

Technical Specification

d-D	M16
k	10
L (mm)	40
P	2
s	24

Technical Drawing

