

Hexagon nut oversized
thread DIN 934 Steel Hot dip
galvanized |8| M12

Article number	01560.120.001
Brand	-
UBB	950355024189
UNSPSC	31161727
EAN	8715492413239
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

Oversized hot dip galvanized nuts are manufactured with thread tolerance class 6AZ and mate with externally threaded parts (bolts, threaded rods) that are manufactured with thread tolerance class 6g before coating.As the nut thread is tapped after galvanizing the threads are not coated. The corrosion resistance however is not influenced disadvantageously as the thread will be protected by the zinc

Standards

DIN	934
NF	E25-401
NEN	1560

Technical Specification

d-D	M12
m	10
P	1.75
s	19

Technical Drawing

