

Hexagon head bolt DIN 931 Steel Plain 10.9 M24X160

Article number	04100.240.160
Brand	-
UBB	950351329350
UNSPSC	31161620
EAN	8715492115713
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	160 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

DIN	931
NF	E25-112
ISO	4014
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	160
P	3
s	36

Technical Drawing

