

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 10.9 M27X80

Article number	04100.270.080
Brand	-
UBB	950351957838
UNSPSC	31161620
EAN	8715492115867
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M27
Length	80 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ISO	4014
DIN	931
ASME	B18.2.3.1M
NEN	1555
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	66
b (min.): L200mm	79
b (min.): L≤125mm	60
d-D	M27
k	17
L (mm)	80
P	3
s	41

Technical Drawing

