

ISO 4014 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 10.9 M8X60

Article number	04101.080.060
Brand	-
UBB	500648295706
UNSPSC	31161620
EAN	8717077206526
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	60 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NEN	1555
DIN	931
ASME	B18.2.3.1M
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	60
P	1.25
s	13

Technical Drawing

