

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 10.9 M24X120

Article number	04102.240.120
Brand	-
UBB	500648139219
UNSPSC	31161620
EAN	8717077209794
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	120 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ISO	4014
NEN	1555
ASME	B18.2.3.1M
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	120
P	3

Technical Drawing



