

Hexagon head bolt DIN 931 Steel Zinc plated 10.9 M24X130



Article number	04102.240.130
Brand	-
UBB	500648139391
UNSPSC	31161620
EAN	8717077209800
PKG. of 10	Full Box Only

Technical Parameters

Diameter (d-D)	M24
Length (L) (mm)	130
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014

Info
 Warning:
 electroplating of
 these products may
 cause hydrogen
 embrittlement.

Technical Specification

b (min.): 125mm<L≤200mm	60
b (min.): L>200mm	73
b (min.): L≤125mm	54
k	15
P	3
s	36

Technical Drawing

