

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Plated, Class 10.9 M24X140

Article number	04102.240.140
Brand	-
UBB	500648139474
UNSPSC	31161620
EAN	8717077209817
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	140 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

DIN	931
NF	E25-112
ASME	B18.2.3.1M
NEN	1555
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	140
P	3

Technical Drawing



