

Hexagon head bolt DIN 931 Steel Zinc plated yellow passivated 10.9 M12X70/ S=19



| | |
|----------------|---------------|
| Article number | 04104.120.070 |
| Brand | - |
| UBB | 952351188661 |
| UNSPSC | 31161620 |
| EAN | 8715493175464 |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|-----------------------|---|
| Diameter (d-D) | M12 |
| Length (L) (mm) | 70 |
| Class | 10.9 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc plated yellow passivated |
| Thread | Metric thread |
| Wrench width (s) (mm) | 19 |
| Info | Warning: electroplating of these products may cause hydrogen embrittlement. |


Standards

| | |
|------|------------|
| ASME | B18.2.3.1M |
| ISO | 4014 |
| NF | E25-112 |
| DIN | 931 |

Technical Specification

| | |
|----------------------------|-----|
| b (min.): 125mm<L≤200mm | 36 |
| b (min.): L>200mm | 49 |
| b (min.): L≤125mm | 30 |
| k | 7.5 |

Technical Drawing



P

1.75

FABORY

19