

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Flake Cr6+ Free, Class 10.9 M6X60

Article number	04105.060.060
Brand	-
UBB	500575130173
UNSPSC	31161620
EAN	8715494313964
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	60 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

NEN	1555
ISO	4014
NF	E25-112
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
k	4
L (mm)	60
P	1
s	10

Technical Drawing

