

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Flake Cr6+ Free, Class 10.9 M10X110

Article number	04105.100.110
Brand	-
UBB	500505561463
UNSPSC	31161620
EAN	8715494439206
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	110 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ISO	4014
ASME	B18.2.3.1M
NEN	1555
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	110
P	1.5

Technical Drawing



